

ORIGINAL BLOW mit 8 Falten

Test Report

Report No.: A 884227-5



DANISH
TECHNOLOGICAL
INSTITUTE

Gregersensvej
DK-2630 Taastrup
Tel. +45 72 20 20 00
Fax +45 72 20 20 19

info@teknologisk.dk
www.teknologisk.dk

Page 1 of 1
Chf/Ieln
Order no.: 884227
No. of appendices: 1

Assignor: Kinnasand GmbH
Danziger Strasse 6
26655 Westerstede
Germany
Attn.: Sonja Fröhlich

Subject: Curtain fabric Art. Blow 6894 (as per info from the assigner).

Sampling: The test material was sampled by the client and received at the Danish Technological Institute 15.08.2019

Method: See Appendix 1.

Period: The testing was completed 09.09.2019

Result: Individual results appear from Appendix 1.

Storage: The test material will be destroyed after 6 months, unless otherwise agreed.

Terms: The accredited test was carried out according to DANAK's general conditions see www.danak.dk and according to the General Terms and Conditions regarding Commissioned Work Accepted by the Danish Technological Institute, which apply at the time of signing the agreement. The test is only valid for the tested specimen. The test report may only be extracted, if the laboratory has approved the extract.

Date/place: 11.09.2019, Danish Technological Institute, Wood and Biomaterials, Textile, Taastrup

Charlotte Fischer

Charlotte Fischer
Ph. Direct: +45 72 20 21 35
E-mail: charlotte.fischer@teknologisk.dk

Lea Larsen

Lea Larsen
Ph. Direct: +45 72 20 21 36
E-mail: leln@teknologisk.dk

Signature: Test responsible

Co-signatory



Report no.: A 884227-5
 Appendix: 1
 Page: 1 of 1
 Initials: Chf/leln

Test Methods	Results
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	001 Colour fastness: 5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	002 Colour fastness: 5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	011 Colour fastness: 4
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	012 Colour fastness: 6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	013 Colour fastness: 4
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	014 Colour fastness: 3 <i>Wurde optimiert</i>
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	021 Colour fastness: 6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	022 Colour fastness: 6-7

⇒ 4-7

Produkt homologation NEUE FARBEN



**DANISH
TECHNOLOGICAL
INSTITUTE**

Test Report

Report No.: A 936737-7

Gregersensvej
DK-2630 Taastrup
Tel. +45 72 20 20 00
Fax +45 72 20 20 19

info@teknologisk.dk
www.teknologisk.dk

Assignor: Kinnasand GmbH
Danziger Strasse 6
D-26655 Westerstede

Page 1 of 1
Chf/Ieln
Order no.: 936737
No. of appendices: 1

Subject: Curtain samples designated: Blow 6894. (as per info from the assigner).

Sampling: The test material was sampled by the client and received at the Danish Technological Institute 30.07.2020

Method: See Appendix 1.

Period: The testing was completed 20.08.2020

Result: Individual results appear from Appendix 1.

Storage: The test material will be destroyed after 6 months, unless otherwise agreed.

Terms: The accredited test was carried out according to DANAK's general conditions see www.danak.dk and according to the General Terms and Conditions regarding Commissioned Work Accepted by the Danish Technological Institute, which apply at the time of signing the agreement. The test is only valid for the tested specimen. The test report may only be extracted, if the laboratory has approved the extract.

Date/place: 21.08.2020, Danish Technological Institute, Wood and Biomaterials, Textile, Taastrup

Digitally signed by:
Charlotte Fischer
Ph. Direct: +45 72 20 21 35
E-mail: chf@teknologisk.dk

Digitally signed by:
Lea Larsen
Ph. Direct: +45 72 20 21 36
E-mail: Ieln@teknologisk.dk

Signature: Test responsible

Co-signatory



Report no.: A 936737-7
 Appendix: 1
 Page: 1 of 2
 Initials: Chf/leln

Test Methods	Results
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0003 Colour fastness: 4-5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0043 Colour fastness: 4-5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0010 Colour fastness: 4-5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0025 Colour fastness: 4-5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0034 Colour fastness: 6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0031 Colour fastness: 4
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0032 Colour fastness: 5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0006 Colour fastness: 4

Report no.: A 936737-7
 Appendix: 1
 Page: 2 of 2
 Initials: Chf/leln

Test Methods	Results
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0014 Colour fastness: 5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0030 Colour fastness: 5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0033 Colour fastness: 3-4
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0024 Colour fastness: 4-5

⇒ 3-7 für alle
Farben

Men: 4-7 (ISO 1-8) 0033 3-4