

# Test Report

Report No.: A 885063-1



**DANISH  
TECHNOLOGICAL  
INSTITUTE**

Gregersensvej  
DK-2630 Taastrup  
Tel. +45 72 20 20 00  
Fax +45 72 20 20 19

info@teknologisk.dk  
www.teknologisk.dk

**Assignor:** Kinnasand GmbH  
Danziger Strasse 6  
D-26655 Westerstede  
Attn.: Sonja Fröhlich

Page 1 of 1  
Chf/Ieln  
Order no.: 885063  
No. of appendices: 1

**Subject:** Curtain fabric Journey 6884(as per info from the assigner).

**Sampling:** The test material was sampled by the client and received at the Danish Technological Institute 21.08.2019

**Method:** See Appendix 1.

**Period:** The testing was completed 23.09.2019

**Result:** Individual results appear from Appendix 1.

**Storage:** The test material will be destroyed after 6 months, unless otherwise agreed.

**Terms:** The accredited test was carried out according to DANAK's general conditions see [www.danak.dk](http://www.danak.dk) and according to the General Terms and Conditions regarding Commissioned Work Accepted by the Danish Technological Institute, which apply at the time of signing the agreement. The test is only valid for the tested specimen. The test report may only be extracted, if the laboratory has approved the extract.

**Date/place:** 24.09.2019, Danish Technological Institute, Wood and Biomaterials, Textile, Taastrup

**Signature:** Test responsible

Co-signatory



Report no.: A 885063-1  
Appendix: 1  
Page: 1 of 2  
Initials: Chf/leln

Test Methods	Results
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	001 Colour fastness: 7
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	002 Colour fastness: 7
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	004 Colour fastness: 4-5
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	003 Colour fastness: 5-6
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	006 Colour fastness: 4
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	011 Colour fastness: 4
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	013 Colour fastness: 4
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	014 Colour fastness: 3-4

Report no.: A 885063-1  
Appendix: 1  
Page: 2 of 2  
Initials: Chf/Ieln

Test Methods	Results
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	015 Colour fastness: 4-5
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	016 Colour fastness: 4
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	033 Colour fastness: 4