

Test Report

Report No.: A 859690-1



**DANISH
TECHNOLOGICAL
INSTITUTE**

Gregersensvej
DK-2630 Taastrup
Tel. +45 72 20 20 00
Fax +45 72 20 20 19

info@teknologisk.dk
www.teknologisk.dk

Assignor: Kvadrat A/S
Lundbergsvej 10
8400 Ebeltøft
Attn.: Lone Henriksen

Page 1 of 1
Chf/leln
Order no.: 859690
No. of appendices: 1

Subject: *GONZEN*
Curtain fabric Winchester, 100% Trevira CS (as per info from the assigner).

Sampling: The test material was sampled by the client and received at the Danish Technological Institute 25.02.2019

Method: See Appendix 1.

Period: The testing was completed 29.03.2019

Result: Individual results appear from Appendix 1.

Storage: The test material will be destroyed after 6 months, unless otherwise agreed.

Terms: Accredited testing was carried out in compliance with international requirements (EN/ISO/IEC 17025:2005) and in compliance with Danish Technological Institute's General Terms and Conditions regarding Commissioned Work accepted by Danish Technological Institute. The test results apply to the tested products only. This report may be quoted in extract only if the laboratory has granted its written consent.

Date/place: 01.04.2019, Danish Technological Institute, Wood and Biomaterials, Textile, Taastrup

Charlotte Fischer

Charlotte Fischer
Ph. Direct: +45 72 20 21 35
E-mail: charlotte.fischer@teknologisk.dk

Signature: Test responsible

Lea Larsen

Lea Larsen
Ph. Direct: +45 72 20 21 36
E-mail: lea.larsen@teknologisk.dk

Co-signatory



Report no.: A 859690-1
 Appendix: 1
 Page: 1 of 2
 Initials: Chf/leln

Test Methods	Results
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0100 / 100 Colour fastness: 7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0500 / 260 Colour fastness: 7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0900 / 160 Colour fastness: 6-7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	1000 / 120 Colour fastness: 6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	B3 / 760 Colour fastness: 7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	B5 / 220 Colour fastness: 7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	D2 Colour fastness: 7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	D9 Colour fastness: 6

Report no.: A 859690-1
 Appendix: 1
 Page: 2 of 2
 Initials: Chf/leln

Test Methods	Results
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	A4 <i>1190</i> Colour fastness: 7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	D4-2 Colour fastness: 7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	A9 <i>1560</i> Colour fastness: 6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	B1 Colour fastness: 7