

Test Report

Report No.: A 826277-1



**DANISH
TECHNOLOGICAL
INSTITUTE**

Gregersensvej
DK-2630 Taastrup
Tel. +45 72 20 20 00
Fax +45 72 20 20 19

info@teknologisk.dk
www.teknologisk.dk

Page 1 of 1
Chf./leln
Order no.: 826277
No. of appendices: 1

Assignor: Kvadrat A/S
Lundbergsvej 10
8400 Ebeltøft
Attn.: Lone Henriksen

Subject: Curtain fabric Campas 300, 100% Trevira CS (as per info from the assigner).

Sampling: The test material was sampled by the client and received at the Danish Technological Institute 22-08-2018

Method: See Appendix 1.

Period: The testing was completed 26-09-2018

Result: Individual results appear from Appendix 1.

Storage: The test material will be destroyed after 6 months, unless otherwise agreed.

Terms: The accredited test was carried out according to DANAK's general conditions see www.danak.dk and according to the General Terms and Conditions regarding Commissioned Work Accepted by the Danish Technological Institute, which apply at the time of signing the agreement. The test is only valid for the tested specimen. The test report may only be extracted, if the laboratory has approved the extract.

Date/place: 26-09-2018, Danish Technological Institute, Wood and Biomaterials, Textile, Taastrup

Charlotte Fischer

Charlotte Fischer
Ph. Direct: +45 72 20 21 35
E-mail: charlotte.fischer@teknologisk.dk

Lea Larsen

Lea Larsen
Ph. Direct: +45 72 20 21 36
E-mail: lea.larsen@teknologisk.dk

Signature: Test responsible

Co-signatory



Report no.: 826277-1
 Appendix: 1
 Page: 1 of 4
 Initials: Chf/leln

Test Methods	Results
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6437/944 Colour fastness: 6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6439/994 Colour fastness: 6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6441 Colour fastness: 6-7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6433 Colour fastness: 5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6434 Colour fastness: 5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6435/764 Colour fastness: 6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6436/794 Colour fastness: 6-7

Report no.: 826277-1
 Appendix: 1
 Page: 2 of 4
 Initials: Chf/leln

Test Methods	Results
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6428/144 Colour fastness: 6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6429 Colour fastness: 5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6431 Colour fastness: 5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6432/734 Colour fastness: 6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6424 Colour fastness: 4-5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6425/184 Colour fastness: 5-6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6426 Colour fastness: 4-5

Report no.: 826277-1
 Appendix: 1
 Page: 3 of 4
 Initials: Chf/leln

Test Methods	Results
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6427/104 Colour fastness: 6-7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6416/564 Colour fastness: 6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6417/664 Colour fastness: 7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6422/124 Colour fastness: 7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6423/154 Colour fastness: 5-6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6411/244 Colour fastness: 6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6412 Colour fastness: 4-5

Report no.: 826277-1
 Appendix: 1
 Page: 4 of 4
 Initials: Chf/leln

Test Methods	Results
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6414/554 Colour fastness: 5-6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6413/684 Colour fastness: 6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6402/444 Colour fastness: 6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6404 Colour fastness: 6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6407/234 Colour fastness: 6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6409/544 Colour fastness: 6

Test Report

Report No.: A 833958-1



**DANISH
TECHNOLOGICAL
INSTITUTE**

Gregersensvej
DK-2630 Taastrup
Tel. +45 72 20 20 00
Fax +45 72 20 20 19

info@teknologisk.dk
www.teknologisk.dk

Page 1 of 1
Chf/leln
Order no.: 833958
No. of appendices: 1

Assignor: Kvadrat A/S
Lundbergsvej 10
8400 Ebeltoft
Attn.: Lone Henriksen

Subject: Curtain fabric Campas
100% Trevira CS (as per info from the assigner).

Sampling: The test material was sampled by the client and received at the Danish Technological Institute 08.10.2018

Method: See Appendix 1.

Period: The testing was completed 26.10.2018

Result: Individual results appear from Appendix 1.

Storage: The test material will be destroyed after 6 months, unless otherwise agreed.

Terms: The accredited test was carried out according to DANAK's general conditions see www.danak.dk and according to the General Terms and Conditions regarding Commissioned Work Accepted by the Danish Technological Institute, which apply at the time of signing the agreement. The test is only valid for the tested specimen. The test report may only be extracted, if the laboratory has approved the extract.

Date/place: 26.10.2018, Danish Technological Institute, Wood and Biomaterials, Textile, Taastrup

Charlotte Fischer

Charlotte Fischer
Ph. Direct: +45 72 20 21 35
E-mail: charlotte.fischer@teknologisk.dk

Lea Larsen

Lea Larsen
Ph. Direct: +45 72 20 21 36
E-mail: lea.larsen@teknologisk.dk

Signature: Test responsible

Co-signatory



Report no.: A 833958-1
 Appendix: 1
 Page: 1 of 1
 Initials: Chf/leln

Test Methods	Results
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6434 E/744 Colour fastness: 6-7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6426 E/194 Colour fastness: 5