



DANISH TECHNOLOGICAL INSTITUTE

Gregersensvej DK-2630 Taastrup Tel. +45 72 20 20 00 Fax +45 72 20 20 19

info@teknologisk.dk www.teknologisk.dk

Page 1 of 1 Chf/leIn Order no.: 822601 No. of appendices: 1

Assignor:

Kvadrat A/S Lundbergsvej 10 8400 Ebeltoft

Attn.: Lone Henriksen

Subject:

Curtain fabric Panorama (as per info from the assigner)

100% Trevira CS

Sampling:

The test material was sampled by the client and received at the Danish Technological In-

stitute 23.07.2018

Method:

See Appendix 1.

Period:

The testing was completed 07.09.2016

Result:

Individual results appear from Appendix 1.

Storage:

The test material will be destroyed after 6 months, unless otherwise agreed.

Terms:

The accredited test was carried out according to DANAK's general conditions see www.danak.dk and according to the General Terms and Conditions regarding Commissioned Work Accepted by the Danish Technological Institute, which apply at the time of signing the agreement. The test is only valid for the tested specimen. The test report may only be extracted if the laboratory has approved the extract.

may only be extracted, if the laboratory has approved the extract.

Date/place:

10.09.2018, Danish Technological Institute, Wood and Biomaterials, Textile, Taastrup

Chailotte Frecher

Charlotte Fischer Ph. Direct: +45 72 20 21 35 E-mail: charlotte.fischer@teknologisk.dk

Signature:

Test responsible

Lea Larsen Ph. Direct: +45 72 20 21 36 E-mail: lea larsen@teknologisk dk





DANISH TECHNOLOGICAL INSTITUTE

Report no.:

822601-1

Appendix: Page: Initials:

1 1 of 4 Chf/leIn

Test Methods	Results	
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6522 Colour fastness:	6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6506/ 201 Colour fastness:	6-7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6507 Colour fastness:	6-7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	Undyed/ 101 Colour fastness:	6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6508/ 611 Colour fastness:	6-7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6509 Colour fastness:	4-5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6510/ 141 Colour fastness:	6



822601-1

Appendix: Page:

Initials:

1 2 of 4 Chf/leIn

Test Methods	Results	
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6511 Colour fastness:	7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6512/ 451 Colour fastness:	6-7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6513 Colour fastness:	6-7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6514 Colour fastness:	5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6515 Colour fastness:	6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6516 Colour fastness:	4
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6517 Colour fastness:	4



Report no.: 822601-1

Appendix: 1
Page: 3 of 4
Initials: Chf/leIn

Test Methods	Results	
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6518 Colour fastness:	7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6519 Colour fastness:	6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6520/ 241 Colour fastness:	6-7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6521/ 711 Colour fastness:	6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6523/ 621 Colour fastness:	6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6524 Colour fastness:	6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6525/ 471 Colour fastness:	6



822601-1

Appendix:
Page:
Initials:

1 4 of 4 Chf/leIn

Test Methods	Results	
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6526/ 651 Colour fastness:	6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6527/ 681 Colour fastness:	6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6528 Colour fastness:	4
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6529 Colour fastness:	5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6530 Colour fastness:	5
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6531 Colour fastness:	4





DANISH TECHNOLOGICAL

Gregersensvej DK-2630 Taastrup Tel. +45 72 20 20 00 Fax +45 72 20 20 19

info@teknologisk.dk www.teknologisk.dk

Page 1 of 1 Chf/leIn Order no.: 831446 No. of appendices: 1

Assignor:

Kvadrat A/S Lundbergsvej 10 8400 Ebeltoft

Attn.: Lone Henriksen

Subject:

Curtain fabric Panorama, 100% Trevira CS (as per info from the assigner).

Sampling:

The test material was sampled by the client and received at the Danish Technological In-

stitute 21-09-2018

Method:

See Appendix 1.

Period:

The testing was completed 09-10-2018

Result:

Individual results appear from Appendix 1.

Storage:

The test material will be destroyed after 6 months, unless otherwise agreed.

Terms:

The accredited test was carried out according to DANAK's general conditions see www.danak.dk and according to the General Terms and Conditions regarding Commissioned Work Accepted by the Danish Technological Institute, which apply at the time of signing the agreement. The test is only valid for the tested specimen. The test report

may only be extracted, if the laboratory has approved the extract.

Date/place: 09-10-2018, Danish Technological Institute, Wood and Biomaterials, Textile, Taastrup

Charlotte Frecher

Charlotte Fischer Ph. Direct: +45 72 20 21 35 E-mail: charlotte.fischer@teknologisk.dk

Signature:

Test responsible

Ph. Direct: +45 72 20 21 36 E-mail: lea.larsen@teknologisk.dk







A 831446-1

Appendix: Page: Initials:

1 1 of 1 Chf/leIn

Test Methods	Results
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6509 E/ 111 Colour fastness: 7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6517E Colour fastness: 5-6
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6529E/ 181 Colour fastness: 6-7
Colour fastness to artificial light DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	6531E/ 771 Colour fastness: 6-7





DANISH TECHNOLOGICAL

INSTITUTE

Gregersensvej DK-2630 Taastrup Tel. +45 72 20 20 00 Fax +45 72 20 20 19

info@teknologisk.dk www.teknologisk.dk

Page 1 of 1 Chf/leln Order no.: 841487 No. of appendices: 1

Assignor:

Kvadrat A/S Lundbergsvej 10 8400 Ebeltoft

Attn.: Lone Henriksen

Subject:

Woven fabric Panorama 981.

100% Trevira CS. (as per info from the assigner).

Sampling:

The test material was sampled by the client and received at the Danish Technological In-

stitute 12.11.2018

Method:

See Appendix 1.

Period:

The testing was completed 05.12.2018

Result:

Individual results appear from Appendix 1.

Storage:

The test material will be destroyed after 6 months, unless otherwise agreed.

Terms:

The accredited test was carried out according to DANAK's general conditions see www.danak.dk and according to the General Terms and Conditions regarding Commissioned Work Accepted by the Danish Technological Institute, which apply at the time of signing the agreement. The test is only valid for the tested specimen. The test report

may only be extracted, if the laboratory has approved the extract.

Date/place: 05.12.2018, Danish Technological Institute, Wood and Biomaterials, Textile, Taastrup

Charlotte Freches

Charlotte Fischer
Ph. Direct: +45 72 20 21 35
E-mail: charlotte.fischer@teknologisk.dk

Signature:

Test responsible







A 841487-1

Appendix: Page: Initials:

1 of 1 Chf/leln

1

Test Methods	Results	
Colour fastness to artificial light DS/EN ISO 105:B02:2014	A Colour fastness:	6
Method 2	Goldan rastiness.	· ·
1-8 scale, 8 best rating Normal conditions		
Apparatus: Atlas Ci4000 Xenon		
Weather-Ometer		
Colour fastness to artificial light	В	
DS/EN ISO 105:B02:2014	Colour fastness:	5-6
Method 2 1-8 scale, 8 best rating		
Normal conditions		
Apparatus: Atlas Ci4000 Xenon		
Weather-Ometer		
Colour fastness to artificial light	C/ 981	
DS/EN ISO 105:B02:2014	Colour fastness:	6
Method 2		
1-8 scale, 8 best rating		
Normal conditions		
Apparatus: Atlas Ci4000 Xenon		
Weather-Ometer		





DANISH TECHNOLOGICAL INSTITUTE

Gregersensvej

DK-2630 Taastrup Tel. +45 72 20 20 00 Fax +45 72 20 20 19

info@teknologisk.dk

www.teknologisk.dk

Page 1 of 1 Chf/leln Order no.: 863632

No. of appendices: 1

Subject:

Assignor:

Curtain fabric Panorama 781, 100% Trevira CS (as per info from the assigner).

Sampling:

The test material was sampled by the client and received at the Danish Technological In-

stitute 19.03.2019

Kvadrat A/S

8400 Ebeltoft

Lundbergsvej 10

Attn.: Lone Henriksen

Method:

See Appendix 1.

Period:

The testing was completed 23.04.2019

Result:

Individual results appear from Appendix 1.

Storage:

The test material will be destroyed after 6 months, unless otherwise agreed.

Terms:

Accredited testing was carried out in compliance with international requirements (EN/ISO/IEC 17025:2005) and in compliance with Danish Technological Institute's General Terms and Conditions regarding Commissioned Work accepted by Danish Technological Institute. The test results apply to the tested products only. This report may be quoted in extract only if the laboratory has granted its written consent.

Date/place: 23.04.2019, Danish Technological Institute, Wood and Biomaterials, Textile, Taastrup

Charlotte Tracher

Charlotte Fischer Ph. Direct: +45 72 20 21 35 E-mail: charlotte.fischer@teknologisk.dk

Signature:

Test responsible

E-mail: lea.larsen@teknologisk.dk







A 863632-1

Report no.: Appendix: Page: Initials:

1

1 of 1 Chf/leln

Test Methods	Results	
Colour fastness to artificial light		
DS/EN ISO 105:B02:2014	Colour fastness:	6
Method 2		_
1-8 scale, 8 best rating		
Normal conditions		
Apparatus: Atlas Ci4000 Xenon		
Weather-Ometer		