

# Test Report

Report No.: A 936737-6



DANISH  
TECHNOLOGICAL  
INSTITUTE

Gregersensvej  
DK-2630 Taastrup  
Tel. +45 72 20 20 00  
Fax +45 72 20 20 19

info@teknologisk.dk  
www.teknologisk.dk

**Assignor:** Kinnasand GmbH  
Danziger Strasse 6  
D-26655 Westerstede

Page 1 of 1  
Chf/IeIn  
Order no.: 936737  
No. of appendices: 1

**Subject:** Curtain samples designated: Even 7079. (as per info from the assigner).

**Sampling:** The test material was sampled by the client and received at the Danish Technological Institute 30.07.2020

**Method:** See Appendix 1.

**Period:** The testing was completed 20.08.2020

**Result:** Individual results appear from Appendix 1.

**Storage:** The test material will be destroyed after 6 months, unless otherwise agreed.

**Terms:** The accredited test was carried out according to DANAK's general conditions see [www.danak.dk](http://www.danak.dk) and according to the General Terms and Conditions regarding Commissioned Work Accepted by the Danish Technological Institute, which apply at the time of signing the agreement. The test is only valid for the tested specimen. The test report may only be extracted, if the laboratory has approved the extract.

**Date/place:** 21.08.2020, Danish Technological Institute, Wood and Biomaterials, Textile, Taastrup

**Signature:** Test responsible

Co-signatory



Report no.: A 936737-6  
Appendix: 1  
Page: 1 of 2  
Initials: Chf/leln

Test Methods	Results
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0006 Colour fastness: 3-4
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0020 Colour fastness: 6
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0012 Colour fastness: 5
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0010 Colour fastness: 6
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0014 Colour fastness: 6
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0011 Colour fastness: 6
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0033 Colour fastness: 5-6
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0013 Colour fastness: 4-5

Report no.: A 936737-6  
 Appendix: 1  
 Page: 2 of 2  
 Initials: Chf/leln

<b>Test Methods</b>	<b>Results</b>
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0001 Colour fastness: 7
<b>Colour fastness to artificial light</b> DS/EN ISO 105:B02:2014 Method 2 1-8 scale, 8 best rating Normal conditions Apparatus: Atlas Ci4000 Xenon Weather-Ometer	0002 Colour fastness: 6